


PERFORATED MEDIA

Instructions for DNP Perforated Instant Printer Media Printing

DNP
Photo Imaging

The printable area of the perforated media is the same as the traditional DNP photo paper but special attention should be noted to maximize the perforation that appears on the paper. Here is some guidance to make the most of it!


DS620 and DS40 4x6' Perforated Media 4x4'



Notes :


- Ideally a 6 mm gutter along the perforated line should be created to allow flexibility with design layouts.

RX1HS 4x6' Perforated Media 2 x (3x2)



- Please note also a 3 mm margin; as this section may be clipped, it should not contain text or important graphics.

RX1HS and DS620 6x8' Perforated Media 3 x (2x8)



Notes :

- Ideally a 6 mm gutter along the perforated line should be created to allow flexibility with design layouts.

- Please note also a 3 mm margin; as this section may be clipped, it should not contain text or important graphics.



DNP PHOTO IMAGING EUROPE
22, avenue des Nations -
Immeuble Raphaël
CS 51077 Villepinte
95948 ROISSY C.D.G. Cedex
FRANCE

Tel : +33 (0)1 49 38 65 50
Fax : +33 (0)1 49 89 00 81
www.dnpphoto.eu